


BACKSHELL KIT INCLUDES:

- (2) BACKSHELL HALVES
- (2) 4-40 THUMBSCREWS
- (2) HOUSING SCREWS/NUTS
- (1) SET OF COMPRESSION INSERTS-VARIOUS SIZES
- DIAMETERS: 4mm (.157"), .5mm (.197"), 7mm (.276"), 9mm (.354")



DIMENSIONS (mm/in)				
SIZE	A $\pm .25$ $\pm .010$	B $\pm .13$ $\pm .005$	C $\pm .25$ $\pm .010$	D $\pm .25$ $\pm .010$
9	31.20	24.99	39.90	15.00
	1.228	0.984	1.571	0.590
	39.50	33.32	41.50	15.00
15	1.555	1.312	1.634	0.590
	53.40	47.04	48.60	15.00
	2.102	1.852	1.913	0.590
25	69.70	63.50	53.60	15.00
	2.744	2.500	2.110	0.590

ORDERING INFORMATION:

SIZE:	P/N - KITTED:	PRODUCT CODE:
9-WAY	6560-0145-01	MHDTPK-9-K
15-WAY	6560-0145-02	MHDTPK-15-K
25-WAY	6560-0145-03	MHDTPK-25-K
37-WAY	6560-0145-04	MHDTPK-37-K

SIZE:	P/N - BULK:	PRODUCT CODE:
9-WAY	6561-0145-01	MHDTPK-9
15-WAY	6561-0145-02	MHDTPK-15
25-WAY	6561-0145-03	MHDTPK-25
37-WAY	6561-0145-04	MHDTPK-37

PLASTIC: ABS POLYLAC - UL RECOGNIZED
NICKEL PLATED
JACKSCREWS: STEEL, Zn PLATED
M3 HOODSCREWS: STEEL, Zn PLATED
COMPRESSION INSERT: ABS UL RECOGNIZED
M3 NUT: STEEL, Zn PLATED
OPERATING TEMP: - 55°C TO 110°C

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF MH CONNECTORS LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	
DRAWN P. JENKINS	DATE 03-14-12
APPROVED D. CROFT	DATE 03-14-12
SCALE NTS	SHEET OF 1 1
DRAWING No MHDTPK SERIES	REV. A

ROHS COMPLIANT



MH CONNECTORS LTD.