





Material	Modified AISI 301 Stainless Steel (0,15 mm thick) front layer with built-in embossed buttons (Ø17mm)
Lettering	Silkscreen printed symbols (epoxy paint)
Button stroke	0,5 mm +/- 0,1 mm
Actuation force	6,0 N (typical)
Life expectancy	>3.000.000 cycles
IP Protection rate	IP65
Impact Protection Rate	IK10
Contact technology	Silver conductive pad on Gold plated PCB
Contact resistance	<100 Ohm
Insulation resistance	>500K Ohm
Contact rating	50 mA ; 25 Vac/dc
Operating temperature	-10°/+70°C
Storage temperature	-25°/+85°C

Compliance: RohS III (2015/863/EU)

Tolerances:			Date	Name	YME MF 12 A	
			04/12	dr		
Revised	05/21	dr			30 26 25	
IP rating	05/19	dr				
Rename	02/14	dr				
Rename	11/13	dr				
Modifications	Date	Name	knitter-switch			Page 1/1