



Part Number : 191640040

Series Number : 19164

Product Category : Quick Disconnects

Product Description : Perma-Seal Male Snap Plug for 14-16 AWG Wire, Diameter 3.96mm, Carton

Status : Active

Engineering Number : SB-289

Documents & Resources

Drawings

Drawing 191640040_sd.pdf

3D Models and Design Files

3D Model 191640040_stp.zip

Specifications

Product Specification PS-19902-011-001.pdf

Product Specification PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19164
Description	Perma-Seal Male Snap Plug for 14-16 AWG Wire, Diameter 3.96mm, Carton
Product Family	Snap Plugs and Receptacles
Product Name	Perma-Seal
Type	Snap Plug
UPC	800753113251

Agency

CSA	LR18689
UL	E152602

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Blue
Gender	Male
Glow-Wire Capable	No
Insulated	Partial
Insulation	NiAc
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.343/g

Orientation	Straight
Packaging Type	Carton
Tab Thickness	N/A
Tab Width	N/A
Temperature Range - Operating	-55° to +125°C
Wire Insulation Diameter	6.71mm max.
Wire Size (AWG)	14, 16

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Insulkrimp Terminals and Splices, 10-22 AWG (Rings, Spades, Hooks, Block Spades and Flanged Spades)	<u>640010300</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640050300</u>

This document was generated on Jul 29, 2024