



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

DESCRIPTION	MATERIAL	FINISH
BODY	BRASS	NICKEL PLATE
CENTER CONTACTS	BRASS	GOLD PLATE
DIELECTRIC	TFE	-
GASKET	RUBBER	-
RETAINING RING	BRASS	NICKEL PLATE

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	04/20/2010	DFRISIELLO
B	ECN 9754: REVISE MODEL AND UPDATE DRAWING AND DIMENSIONS	03/20/2019	DFRISIELLO



Ø .79
[20.0]




NOTES:

ELECTRICAL:
IMPEDANCE: 50 OHMS
FREQUENCY RANGE: DC ~ 11 GHz
VOLTAGE RATING: 500 VOLTS PEAK
DIELECTRIC WITHSTANDING VOLTAGE: 1000 VOLTS RMS

MISCELLANEOUS:
COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN
ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: X = ± .2 [5.08] XX = ± .02 [51] XXX = ±.005 [1.3] PROJECTION 	APPROVALS	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845		
	DRAWN BY DFRISIELLO	04/20/2010			
	CHECKED BY K.BURGNER	04/20/2010	CATEGORY	COAXIAL	
	APPROVED BY K.BURGNER	04/20/2010			
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION		ADAPTER,TYPE N-MALE TO TYPE TNC FEMALE		
	COLOR VARIATIONS MAY OCCUR				
	SIZE A	FSCM NO. 43321	DWG. NO. AXA-NMTF	REV. B	
SCALE: NONE		CAD FILE: AXA-NMTF.SLDDRW		SHEET 1 OF 1	