



Color: ■ gray

Electrical data

Ratings per IEC/EN	
Rated current	10 A

Physical data

Width	8 mm / 0.315 inches
Height	10 mm / 0.394 inches
Depth	4 mm / 0.157 inches
Jumper assignment	1-2

Material data

Note (material data)	Information on material specifications can be found here
Color	gray
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.005 MJ
Weight	0.4 g



Environmental requirements		
Processing temperature		-35 ... +85 °C
Continuous operating temperature		-60 ... +105 °C

Commercial data		
Product Group		9 (Std Chassis Mt Blocks)
PU (SPU)		500 (25) pcs
Packaging type		Box
Country of origin		PL
GTIN		4045454030858
Customs tariff number		85366990990

Product Classification		
UNSPSC		39121421
eCl@ss 10.0		27-14-11-40
eCl@ss 9.0		27-14-11-40
ETIM 9.0		EC000489
ETIM 10.0		EC000489
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 260-402

↓

Documentation				
Bid Text				
260-402	19.02.2019	xml 2.62 KB		↓
260-402	17.08.2017	doc 23.50 KB		↓




CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 260-402	EPLAN Data Portal 260-402
	WSCAD Universe 260-402
	ZUKEN Portal 260-402

1 Compatible Products
1.1 Optional Accessories
1.1.1 Tool
1.1.1.1 Operating tool



Item No.: 209-132
Operating tool; for connecting comb-style jumper bar; made of insulating material; 2-way; natural

Installation Notes
Commoning



Commoning with comb-style jumper bar.