

Coaxial Panel Connector 23_N-50-0-16/133_N

Description

Straight panel receptacle jack, flange mount

Interface standards
IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 11 GHz

Mechanical Data

Number of matings 500
Weight 0.0141 kg

Environmental Data

Operating temperature -65 °C to 125 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00010111
Catalogue drawing DCA-00010113

Ordering Information

Single package 23_N-50-0-16/133_NE