

**Part Number :** [797580007](#)

**Product Description :** Pre-Crimped Lead KK 254  
Female-to-KK 254 Female, Tin (Sn) Plating, 150.00mm  
Length, 22 AWG, Black

**Series Number :** 79758

**Status :** Obsolete

**Product Category :** Power and Signal Cable  
Assemblies



---

## Documents and Resources

### Drawings

[797580007\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |                                                 |
|--------------------|-------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                    |
| China RoHS         | per SJ/T 11365-2006                             |
| EU ELV             | Not Relevant                                    |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21              |
| REACH SVHC         | Not Contained per D(2025)4165-DC (25 June 2025) |
| EU RoHS            | Compliant per EU 2015/863                       |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## Part Details

### General

|                        |                                                                                                   |
|------------------------|---------------------------------------------------------------------------------------------------|
| Status                 | Obsolete                                                                                          |
| Category               | Power and Signal Cable Assemblies                                                                 |
| Series                 | 79758                                                                                             |
| Description            | Pre-Crimped Lead KK 254 Female-to-KK 254 Female, Tin (Sn) Plating, 150.00mm Length, 22 AWG, Black |
| Assembly Configuration | Pre-crimped Lead Only                                                                             |
| Connector to Connector | KK Crimp Terminals                                                                                |
| Keyword                | Pre-Crimped Leads                                                                                 |
| Product Name           | KK                                                                                                |
| UPC                    | 884982052703                                                                                      |

### Physical

|                                |                      |
|--------------------------------|----------------------|
| Cable Length                   | 150.00mm             |
| Circuits (Loaded)              | 1                    |
| Circuits (maximum)             | 1                    |
| Color - Resin                  | Black                |
| Gender                         | Female-Female        |
| Material - Metal               | Brass                |
| Material - Plating Mating      | Tin                  |
| Material - Plating Termination | Tin                  |
| Net Weight                     | 0.804/g              |
| Packaging Type                 | Bag                  |
| Single Ended                   | No                   |
| Termination Interface Style    | Crimp or Compression |
| Wire/Cable Type                | UL 1061              |
| Wire Size (AWG)                | 22                   |

## Mates With / Use With

**Use with Part(s)**

| Description                      | Part Number |
|----------------------------------|-------------|
| KK 254 Single Row Crimp Housings | <u>2695</u> |

This document was generated on Oct 10, 2026

Obsolete