

Specifications

Photo is representative

Eaton SMS3R1

Panel mount receptacle; SMS3R1

General specifications

PRODUCT NAME	Eaton Souriau SMS series quick mating plastic rectangular connector
CATALOG NUMBER	SMS3R1
PRODUCT LENGTH/DEPTH	25 mm
PRODUCT HEIGHT	15.2 mm
PRODUCT WIDTH	16.2 mm
PRODUCT WEIGHT	2.3 g
PRODUCT TYPE	Quick mating plastic rectangular connector

Product specifications

ENVIRONMENTAL CONDITIONS	Flammability rating UL94
	V0
	RoHS
	REACH

CONNECTOR ACCESSORY OPTION	No backshell possibility
---------------------------------------	--------------------------

CONNECTOR TYPE	Receptacle
-----------------------	------------

CONTACT DELIVERY	Not delivered
-------------------------	---------------

CONTACT TYPE	Crimp
---------------------	-------

COUPLING TYPE	Push-Pull
----------------------	-----------

DEGREE OF PROTECTION	IP30
-----------------------------	------

LAYOUT	3
---------------	---

SHELL MATERIAL	Plastic
-----------------------	---------

OPERATING TEMPERATURE - MAX	125 °C
--	--------

OPERATING TEMPERATURE - MIN	-55 °C
--	--------

RECEPTACLE TYPE	Front Mount Panel
------------------------	-------------------

NUMBER OF CONTACTS	3
---------------------------	---

NUMBER OF CAVITY #16	3
-----------------------------	---

Resources

DRAWINGS	SMS-SE72097.pdf
----------	---------------------------------

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

