

Product Line

DeepTronica >

Single Pair Ethernet >

ZConnect >

Ceres >

X-Lok >

Accessory

Middle Size

Mini Size

Large Size

Standard Size

M Series >

FLOS & FLOS+ >

Power >

RBL >

HS-Lok >

NMEA 2000 >

Heavy Duty Shielded >

RJ >

USB >

SSL >

HDMI >

DVI >

Fiber Optic >

RF >

Cable Joiner >

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >



CBD-08PMFS-QC8001

Operating Temperature: -40°C ~ +105°C
Transmission Speed: N/A
Shielded: Plastic, Non-shielded
Jacket Material: N/A
Certificate: UL1977


You must login first for view the price

Quantity - 1 +

 Check Stock

 Add to Cart

 Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type ▼ Search



X-Lok, Middle Siz...
AB-CBD08BL-...
-40°C ~ +105°C

- 0 +

☐



X-Lok, Middle Siz...
AB-CBD08BL-...
-40°C ~ +105°C

- 0 +

☐



X-Lok, Middle Siz...
AB-CBD08BL-...
-40°C ~ +105°C

- 0 +

☐



X-Lok, Middle Siz...
AB-CBD08BL-...
-40°C ~ +105°C

- 0 +

☐



X-Lok, Middle Siz...
AB-CBD08BL-...
-40°C ~ +105°C

- 0 +

☐



X-Lok, Middle Siz...
AB-CBD08BL-...
-40°C ~ +105°C

- 0 +

☐

Add to Cart Inquiry

Specifications	Download / CAD
Nominal Current 10A+5A	Connector Type Receptacle
Shielded Plastic, Non-shielded	No. of Contacts 08
Connector Gender Male	Backshell Circular
Mating Style Push Lock	IP Rating IP68
Assembly Style Solder	
➕ More Options	

People Also Bought



CBD-08PMFS-QC8001



MSAS05ML-SASFL-...



MSAP-05BMMM-...



AB-CD07HL-CDBR-...



MSAS-06PFPF-...