


OA172SAP XC Salt Fog Series




AC Fans - 115, 230V
172mm x 150mm x 55mm
(6.7" x 5.9" x 2.2")



Units: mm

Frame	Die Cast Aluminum, Black Finish	<u>Operating Temperature</u> -40°C ~ +50°C 25% ~ 85% Non-Condensing R.H. <u>Storage Temperature</u> -40°C ~ +80°C 20% ~ 85% Non-Condensing R.H. <u>Life Expectancy</u> 40,000 Hours (L10 at 40°C) <u>Environmental Protection</u> Salt Fog IP55 Rated (GR-487) Weight: 2.31 lbs.
Impeller	PC, UL94 V-0 Plastic	
Connection	Fan Terminals	
Motor	AC, Capacitor Induction, Single Phase, Thermally Protected, Class B Insulation, IP55 Salt Fog	
Bearing System	Dual Ball Bearings	
Insulation Resistance	1500VAC/min, <1mA	
Dielectric Strength	$\geq 100\text{M}\Omega @ 500\text{V DC}$	



Part Number	Rated Voltage (Volts AC)	Voltage Range (Volts AC)	Input Power (Watts)	Rated Current (Amps)	Frequency (Hertz)	Rated Speed (RPM)	Max Airflow (CFM)	Noise Level (dBA)	Max Static Pressure ("H ₂ O")
OA172SAP-11-1TBXCSF	115	105 ~ 126	40 / 39	0.38 / 0.34	50 / 60	2850 / 3375	240 / 293	58 / 63	0.65 / 0.90
OA172SAP-22-1TBXCSF	230	210 ~ 255	41 / 40	0.20 / 0.18	50 / 60	2850 / 3375	240 / 293	58 / 63	0.65 / 0.90