


MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-RW8405-A2



NOTE -
 $\triangle$ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON $1.000 \pm .002$ CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

CHARACTERISTICS

OPERATING FORCE ----- $3/4$ OZ MAX

RELEASE FORCE ----- $1/8$ OZ MIN

DIFFERENTIAL TRAVEL ----- .003 - .015

OVERTRAVEL ----- .219 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L103 15A 125, 250 OR 480 VAC
1/8HP 125 VAC, 1/4HP 250 VAC

L288
L299
L306



16A 250V $\sim$ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE 2

DES.	TOL.	DES.	TOL.
mm	mm/10	in	mm/10
1ST PLACE	X	1/64	
2ND PLACE	X, X	0.0010	X, X
3RD PLACE	X, X	0.0005	X, X
4TH PLACE	X, X	0.0001	X, X

DESIGN UNITS ☐ METRIC ☒ US CUSTOMARY

WEIGHT .073 LB.

CATALOG LISTING

BZ-RW8405-A2

PAGE 1 OF 1

M

ISSUE 3

REVISIONS

A	CO-73287-J	JAL	22 NOV 93
B	203155	CSL	24 MAY 01

CHECK

FO-52848-A	DRAWN	GJW	14 MAY 81	CHECK	CEB	16 MAY 81	CHECK	16 MAY 81
------------	-------	-----	-----------	-------	-----	-----------	-------	-----------


MASTER

MICRO SWITCHFREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC


CATALOG LISTING

BZ-RW8405 - A 2**NOTE -**

① - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON $1.000 \pm .002$ CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

**CHARACTERISTICS**OPERATING FORCE ----- $3/4 \text{ OZ MAX}$ RELEASE FORCE ----- $1/8 \text{ OZ MIN}$ DIFFERENTIAL TRAVEL ----- $.003 - .015$ OVERTRAVEL ----- $.219 \text{ MIN}$ **ELECTRICAL DATA**

CONTACT ARRANGEMENT

S P D T

UL LISTED - FILE E12252
CODE L103 15A-125, 250 OR 480 VAC
1/8HP-125 VAC; 1/4HP-250 VAC



SCALE FULL

DO NOT SCALE PRINT

TOLERANCESAPPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE ± 2

	DIM. in	TOL. in	DIM. mm	TOL. mm
ONE PLACE	X	1/100	X	0.025
TWO PLACES	X, X	0.0010	X, X	0.025/010
THREE PLACES	X, X, X	0.00010	X, X, X	0.025/0010

DESIGN UNITS

IN METRIC

US CUSTOMARY

WEIGHT .073 LB.

BZ-RW8405-A2
M
DRAWING NUMBER
2
X
ISSUE
REVISIONS
A CO-73287-J
JAL
22 NOV 93
FO-52848-A
DRAWN
GJW
14 MAY 81
CHECK
CEB
16 MAY 81
CHECK
X72363-BZ
REPLACES
PR-10186
RELEASE NO.