


DESCRIPTION: 979 SERIES D-SUB BACKSHELL - METALIZED PLASTIC

DIMENSIONS (mm)


SIZE	A ^{±0.3}	B ^{±0.3}	C ^{±0.3}	D ^{±0.3}	E ^{±0.3}
9	31.20	24.99	47.90	16.60	10.20
15	39.30	33.30	48.20	16.60	10.20
25	53.50	47.10	44.80	17.30	13.00
37	69.80	63.49	48.50	16.60	13.00
50	67.60	61.00	48.50	19.30	13.00

BACK SHELL KIT INCLUDES:

- 2 - BACK SHELL HALVES
- 2 - MATING SCREWS (#4-40, RECOMMENDED TORQUE 60 in-oz)
- 2 - SADDLE WASHERS
- 2 - HOUSING SCREWS (#4-40, RECOMMENDED TORQUE 5.2 in-lbs)
- 2 - HOUSING NUTS (#4-40, RECOMMENDED TORQUE 5.2 in-lbs)
- 1 - GROMMET TREE - SEE PAGE 2 (NON-CONDUCTIVE GROMMETS)



BACKSHELL MATERIAL: NICKEL PLATED ABS PLASTIC, UL 94HB
HARDWARE MATERIAL: NICKEL PLATED STEEL
GROMMET MATERIAL: TPR
OPERATING TEMPERATURE: 0°C TO +80°C



RoHS COMPLIANT



Downloaded from Arrow.com

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: P. JENKINS
DATE: 07/28/2005

UNITS = mm






DO NOT SCALE FROM DRAWING

SCALE: NTS

SHEET 1 OF 2

REV 8

DWG NO. 979-YYY-020R121



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
P. JENKINS

DATE:
07/28/2005

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:
NTS

SHEET OF
2 2

REV
8

DWG NO.

979-YYY-020R121