

Product Line

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- Accessory
- M5
- Guided M8
- M8
- M10.5
- M12 (A)
- M12 (B)
- M12 (D)
- M12 (I)
- M12 (K)
- M12 (L)
- M12 (S)
- M12 (T)
- M12 (X)
- M23
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



MSAP-03BFFA-SL8001

Operating Temperature: -40°C ~ +105°C
Transmission Speed: N/A
Shielded: Plastic, Non-shielded
Jacket Material: N/A
Certificate: UL1977, UL2238, UL1863

You must login first for view the price

Quantity - 1 +

Add to Cart Inquiry 

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type Search



Ceres, Accessory...
TOL-151701
N/A

- 0 +

☐



Ceres, Accessory...
TOL-151702
N/A

- 0 +

☐



M Series...
CAP-WBDFSM A1
-40°C ~ +105°C

- 0 +

☐

Add to Cart Inquiry

Specifications	Download / CAD
Nominal Current 4A	Connector Type Field Installable
Shielded Plastic, Non-shielded	No. of Contacts 03
Connector Gender Female	Backshell Straight
Mating Style Screw Thread	IP Rating IP68
Assembly Style Solder	
More Options	

People Also Bought

- 

MSAP-03BFFA-...
- 

AB-DCD12FR-DCDFR...
- 

GBD-08AFFM-TL8A01
- 

CD-08RFFS-RC8CA0
- 

M12B-04BMMA-...