



B

B



Crimp Contacts To  
.237 ±0.005 at both ends



| DATE     | REV | ECN       | APP'D. BY |
|----------|-----|-----------|-----------|
| 02/22/19 | A0  | RELEASED  | ET        |
| 02/22/19 | A1  | ECN 11349 | TLS       |
| 01/24/20 | A2  | 11503     | JE        |

### Notes:

- 1) Each cable assembly to be individually bagged.
- 2) 50μ" Gold plating on contacts
- 3) Cable Construction:
  - 24 AWG Stranded
  - 4Pr, U/UTP, Type CM
  - PVC Jacket
- 4) 100% Transmission Tested for Performance

### P/N Key:


BM-6UxxxxF

UOM  
F = Feet

Color  
E = Blue  
G = Grey

| Length |      |
|--------|------|
| XXX    | Feet |
| 001    | 1    |
| 003    | 3    |
| 005    | 5    |
| 007    | 7    |
| 010    | 10   |
| 015    | 15   |
| 025    | 25   |


### Wiring Map: 568B Standard



### Example Parts Numbers

| Feet       |       |        |
|------------|-------|--------|
| P/N        | Color | Length |
| BM-6UG001F | Grey  | 1'     |
| BM-6UE010F | Blue  | 10'    |

For Part Numbers Not Shown Follow Part Number Key Format



|                                                                              |  |                                                                                                                                                                                                                                          |               |
|------------------------------------------------------------------------------|--|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| THIRD ANGLE PROJECTION<br>                                                   |  | <br>206 Van Vorst Street<br>Jersey City, NJ 07302<br>+1 201 432 0463<br><a href="http://www.belfuse.com">http://www.belfuse.com</a>                                                                                                      |               |
| DO NOT SCALE DRAWING<br>DRAWING IS SUBJECT TO<br>CHANGE WITHOUT NOTICE       |  | TITLE: Bel Patchcord Assembly, C6 U/UTP, 24 awg<br>Component Compliant                                                                                                                                                                   |               |
| DIMENSIONS: INCHES [METRIC]                                                  |  | THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON<br>ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF<br>BEL FUSE, INC. AND SHALL NOT BE REPRODUCED,<br>COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN<br>CONSENT OF BEL FUSE, INC. |               |
| UNLESS OTHERWISE SPECIFIED<br>TOLERANCES ARE ±.005 [0.13]<br>ANGLES ARE ± 1° |  | DRN BY: TLS                                                                                                                                                                                                                              | DATE 02/22/19 |
| SHEET NO. 1 OF 1                                                             |  | APPD BY: ET                                                                                                                                                                                                                              | DATE 02/22/19 |
|                                                                              |  | DWG NO. CT999183                                                                                                                                                                                                                         | REV. A2       |

A

A