


Hex nuts ~0,8d

BN 628



Standard

DIN 934 (Standard withdrawn), ~ISO 4032, ~UNI 5588, ~ČSN 021401

Additional information

The commercial quality is class A2-70 / A4-70 (tensile strength 700 N/mm²) for M5-M24.

Material

Stainless steel

Material type

A2

Article no.	d1	e min.	s	m max.
1421786	M1	2,71	2,5	0,8
1421794	M1,2	3,28	3	1
1421808	M1,4	3,28	3	1,2
1241389	M1,6	3,41	3,2	1,3
1241397	M2	4,32	4	1,6
1241419	M2,3	4,88	4,5	1,8
1241427	M2,5	5,45	5	2
1241435	M2,6	5,45	5	2
1241443	M3	6,01	5,5	2,4
1241451	M3,5	6,58	6	2,8
1241478	M4	7,66	7	3,2
1241486	M5	8,79	8	4
1241494	M6	11,05	10	5
1241508	M8	14,38	13	6,5
1241516	M10	18,9	17	8
1241524	M12	21,1	19	10
1241532	M14	24,49	22	11
1241540	M16	26,75	24	13
1241559	M18	29,56	27	15
1241567	M20	32,95	30	16
1241575	M22	35,03	32	18
1241583	M24	39,55	36	19

Article no.	d1	e min.	s	m max.
1241591	M27	45,2	41	22
1241605	M30	50,85	46	24
1397354	M33	55,37	50	26
1129333	M36	60,79	55	29
1210114	M42	71,3	65	34