


Data Sheet | Item Number: 216-202

Ferrule; Sleeve for 0.75 mm² / 18 AWG; insulated; electro-tin plated; gray

<https://www.wago.com/216-202>



Color:  gray

Similar to illustration

Dimensions in mm

Connection Data

Metric cross-section of the ferrule	0.75 mm ²
Strip length	10 ... 11 mm / 0.39 ... 0.43 inches
Cross-section (AWG) of ferrule	18 AWG

Physical data

Total length (L)	14 mm
Wall thickness of crimp sleeve (W2)	0.15 mm
Wall thickness (plastic collar W1)	0.25 mm
Crimp length (length of sleeve L1)	8 mm
Inner diameter of plastic collar (D1)	2.8 mm
Diameter crimp sleeve inside (D2)	1.2 mm

Mechanical data

Plastic collar	Standard collar
----------------	-----------------

Material data

Color	gray
Fire load	0.001 MJ
Weight	0.1 g



Commercial data	
Product Group	2 (Terminal Block Accessories)
PU (SPU)	1000 pcs
Packaging type	Box
Country of origin	DE
GTIN	4017332277457
Customs tariff number	85369010000

Product Classification	
UNSPSC	39121405
eCl@ss 10.0	27-40-02-01
eCl@ss 9.0	27-40-02-01
ETIM 9.0	EC000005
ETIM 10.0	EC000005
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 216-202

↓

Documentation			
Bid Text			
216-202	19.02.2019	xml 2.80 KB	↓
216-202	11.09.2017	doc 23.50 KB	↓

CAD/CAE-Data


CAD data

2D/3D Models 216-202

↓



Installation Notes



A perfect gas-tight crimp – both electrically and mechanically reliable