

Product Line

- Single Pair Ethernet >
- ZConnect >
- Ceres >
- Accessory
- Large Size
- Macro Size
- Middle Size
- Mini Size
- Others (GBD)
- Others (MAB)
- Others (PLD)
- Standard Size
- X-Lok >
- M Series >
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >



ACC-03RMMS-LC7001

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: N/A

Certificate: N/A

You must login first for view the price

Quantity

- 1 +

Add to Cart

Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

ABOUT AMPHENOL LTW

SUPPORT

PARTNERS

DOWNLOAD CENTER

FEEDBACK

- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >

Add to Cart

Inquiry

Specifications	Download / CAD
Nominal Current 20A	Connector Type Receptacle
Shielded Plastic, Non-shielded	No. of Contacts 03
Connector Gender Male	Backshell Circular
Mating Style 2 Points Lock	IP Rating IPX7
Assembly Style Solder	
More Options	

People Also Bought

