



BU-1420701211 (CONN SMA JACK STR 50 OHM PCB)



Mueller Electric Company
2850 Gilchrist Rd. Bld 5A
Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629
Phone: 330.780.2525
Fax: 330.780.2524



(Dimensions in Inches)

- Impedance: 50 Ohms
- Frequency Range: 0-18GHz
- Working Voltage: 335V at Sea Level
- Dielectric Withstanding Voltage: 1000V min at sea level
- Contact resistance: 3 milliohms
- Mating Torque: 7-10 Inch Pounds
- Material:
 - Body –Brass with 1U' Gold plated
 - Contact –Beryllium Copper with 3U' Gold plated
 - Insulator – Teflon
- Meets or Exceeds the applicable paragraph of MIL-C-39012
- Operating Temperature: -65°C (-85°F) to 150°C (302°F)
- RoHS 3 Compliant