



74LVC11PW-Q100

Triple 3-input AND gate

The 74LVC11-Q100 provides three 3-input AND functions.

This product has been qualified to the Automotive Electronics Council (AEC) standard Q100 (Grade 1) and is suitable for use in automotive applications.

Download datasheet

Buy online

Product details

Documentation

Support

Ordering

Features

- Automotive product qualification in accordance with AEC-Q100 (Grade 1)
- Specified from -40 °C to +85 °C and from -40 °C to +125 °C

Target applications

Show more

Parametrics

Type number	Product status	Package name
74LVC11PW-Q100	Production	TSSOP14

Package

Type number	Package	Outline version	Reflow-/Wave soldering	Packing	Status	Marking	Orderable part number, (Ordering code (12NC))
74LVC11PW-Q100	 TSSOP14 (SOT402-1)	<u>SOT402-1</u>	<u>SSOP-TSSOP-VSO-WAVE</u>	<u>Reel 13" Q1/T1</u>	Active	Standard Marking	74LVC11PW-Q100J (9356 903 55118)

Quality, reliability & chemical content

Type number	Orderable part number	Chemical content	RoHS / RHF	Leadfree conversion date	MSL	MSL leadfree
74LVC11PW-Q100	74LVC11PW-Q100J	Not available				

Series

 [74LVC11-Q100 - Triple 3-input AND gate](#)