


432EC6W

Industrial Connector

2CMA101159R1000



Industrial Connectors, 3P+N+E, IP67, 32 A, 200/346 ...
240/415 V

GENERAL

Product Name	Industrial Connector
Product ID	2CMA101159R1000
Function	Connector
EAN	73926911594
Catalog Description	Industrial Connectors, 3P+N+E, 32 A, 200/346 ... 240/415 V
Country of Origin	Czech Republic (CZ)
E-Number Finland	2420094
E-Number Norway	1540731
E-Number Sweden	E2417296
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	EC
Color	Red
Number of Poles	5
Clock Position	6Hour
Rated Current	32 ampere
Rated Voltage	200/346 ... 240/415 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67
Cable Cross-Section	2.5...6 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	99 millimetre
Product Net Height	99 millimetre
Product Net Length	195 millimetre
Product Net Depth	195 millimetre
Product Net Weight	0.30 kilogram

PACKAGING

Package Width	410 millimetre
Package Height	195 millimetre
Package Gross Weight	3 kilogram
Package Length	190 millimetre
Package Units	box 10 piece