


**Data Sheet | Item Number: 216-267**

Ferrule; Sleeve for 4 mm<sup>2</sup> / AWG 12; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray

<https://www.wago.com/216-267>



Color: ■ gray

Similar to illustration

Dimensions in mm

| Connection Data                     |  |                                     |
|-------------------------------------|--|-------------------------------------|
| Metric cross-section of the ferrule |  | 4 mm <sup>2</sup>                   |
| Strip length                        |  | 14 ... 15 mm / 0.55 ... 0.59 inches |
| Cross-section (AWG) of ferrule      |  | 12 AWG                              |

| Physical data                         |  |        |
|---------------------------------------|--|--------|
| Total length (L)                      |  | 20 mm  |
| Wall thickness of crimp sleeve (W2)   |  | 0.2 mm |
| Wall thickness (plastic collar W1)    |  | 0.3 mm |
| Crimp length (length of sleeve L1)    |  | 12 mm  |
| Inner diameter of plastic collar (D1) |  | 4.8 mm |
| Diameter crimp sleeve inside (D2)     |  | 2.8 mm |

| Mechanical data |  |                     |
|-----------------|--|---------------------|
| Plastic collar  |  | Standard collar     |
| Suitable        |  | 2004 to 2006 Series |

| Material data |  |          |
|---------------|--|----------|
| Color         |  | gray     |
| Fire load     |  | 0.001 MJ |
| Weight        |  | 0.2 g    |

| Commercial data       |                                |
|-----------------------|--------------------------------|
| Product Group         | 2 (Terminal Block Accessories) |
| PU (SPU)              | 500 (100) pcs                  |
| Packaging type        | Bag                            |
| Country of origin     | DE                             |
| GTIN                  | 4055143654739                  |
| Customs tariff number | 85369010000                    |

| Product Classification |                      |
|------------------------|----------------------|
| UNSPSC                 | 39121405             |
| eCl@ss 10.0            | 27-40-02-01          |
| eCl@ss 9.0             | 27-40-02-01          |
| ETIM 9.0               | EC000005             |
| ETIM 10.0              | EC000005             |
| ECCN                   | NO US CLASSIFICATION |

| Environmental Product Compliance |                         |
|----------------------------------|-------------------------|
| RoHS Compliance Status           | Compliant, No Exemption |

Downloads

Environmental Product Compliance


Compliance Search

Environmental Product Compliance 216-267

↓

| Documentation |            |                 |   |
|---------------|------------|-----------------|---|
| Bid Text      |            |                 |   |
| 216-267       | 19.02.2019 | xml<br>2.80 KB  | ↓ |
| 216-267       | 11.09.2017 | doc<br>24.00 KB | ↓ |

Installation Notes



A perfect gas-tight crimp – both electrically and mechanically reliable