


TF31 Series

TF31-22S-0.5SH(800)CL0480-0143-9-00

RoHS2



※ The actual product may differ from the image

- ▶ Document

PART NUMBER CONFIGURATION

Part No.	TF31-22S-0.5SH(800)
Connector Type	Receptacle
Mounting Pitch	0.5 mm
Connector Length	15.3 mm
Connector Height	2.0 mm

2D

3D MODEL (IGES)

3D MODEL (STEP)

☑

INVENTORY

PRODUCT NUMBERS BY SERIES

CONTACT US

Detailed Specifications

Last Updated On March. 25, 2021

▼ Product information			
Part No.	TF31-22S-0.5SH(800)	CL No.	CL0480-0143-9-00
▶ Basic Specifications			
▶ Mechanical Specifications			
▶ Electrical Specifications			
▶ Dimensional Information			
▶ Packaging Specifications			
▶ Others			

Document

In cases where the application will demand a high level of reliability, such as automotive, please contact a company representative for further information.

Catalog

- Series Catalog - English [TF31-22S-0.5SH(800)_CL0480-0143-9-00_Catalog_D51105_en.pdf: 1,184 KB]

• Series Catalog - 日本語 [TF31-22S-0.5SH(800)_CL0480-0143-9-00_Catalog_D51105_ja.pdf: 1,273 KB]

Data Sheet

- Drawing (2D) - English [TF31-22S-0.5SH(800)_CL0480-0143-9-00_2DDrawing_TF31-ALLS-0.5SH(800)_2D_Eng_200701.pdf: 724 KB]

• Drawing (2D) - 日本語 [TF31-22S-0.5SH(800)_CL0480-0143-9-00_2DDrawing_TF31-ALLS-0.5SH(800)_2D_JP_200701.pdf: 679 KB]

• Specification Sheet - English [TF31-22S-0.5SH(800)_CL0480-0143-9-00_SpecSheet_D141230_en.pdf: 64 KB]

• Specification Sheet - 日本語 [TF31-22S-0.5SH(800)_CL0480-0143-9-00_SpecSheet_D141230_ja.pdf: 282 KB]

• Drawing (3D) (IGES) [TF31-22S-0.5SH(800)_CL0480-0143-9-00_3DDrawing_IGES_D51154_ja.zip: 418 KB]

• Drawing (3D) (STEP) [TF31-22S-0.5SH(800)_CL0480-0143-9-00_3DDrawing_STEP_D127064_ja.zip: 202 KB]