



Products

Customize Your Parts

Industries Solutions

Search

News & Events

First Time?



(0)



Home / Products / M Series / Accessory

Product Line

DeepTronica >

Single Pair Ethernet >

ZConnect >

Ceres >

X-Lok >

M Series >

Accessory

M5

Guided M8

M8

M10.5

M12 (A)

M12 (B)

M12 (D)

M12 (I)

M12 (K)

M12 (L)

M12 (S)

M12 (T)

M12 (X)

M23

FLOS & FLOS+ >

Power >

RBL >

HS-Lok >

NMEA 2000 >

Heavy Duty Shielded >

RJ >

USB >

SSL >

HDMI >

DVI >

Fiber Optic >

RF >

Cable Joiner >

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >



CAP-WBBFSPC1

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: N/A

Certificate: N/A

You must login first for view the price

Quantity - 1 +

 Add to Cart

 Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

 Search



M Series, Guided...
8AP-04AFFM-...
-20°C ~ +85°C

- 0 +

☐



M Series, Guided...
8AP-04AFFM-...
-20°C ~ +85°C

- 0 +

☐



M Series, Guided...
8AP-04AFFM-...
-20°C ~ +85°C

- 0 +

☐



M Series, Guided...
8AP-04AFFM-...
-20°C ~ +85°C

- 0 +

☐



M Series, Guided...
8AP-05AFFM-...
-20°C ~ +80°C

- 0 +

☐



M Series, Guided...
8AP-05AFFM-...
-20°C ~ +80°C

- 0 +

☐

 Add to Cart

 Inquiry

Specifications

Download / CAD

Nominal Current

N/A

Connector Type

Waterproof Cap

Shielded

Plastic, Non-shielded

No. of Contacts

N/A

Connector Gender

Female

Backshell

N/A

Mating Style

Screw Thread

IP Rating

N/A

Assembly Style

With Rubber Lead

 [More Options](#)

People Also Bought



CAP-WBBFSPC1



M12A05ML-12AFL-...



DD-09RFFS-RC8C10



M12S-04BMMM-...



1BD-04AFMM-SL6A10