









ALTERNATIVE DESIGN C



PART NUMBER	LC2 ADAPTER	ADAPTER COLOR
EHLC2	SINGLE-MODE	BLUE
EHLC2M	MULTI-MODE	BEIGE



- NOTES:
- D 1. INSERTION LOSS - SINGLE MODE: 0.2 dB MAX
MULTI-MODE: 0.3 dB MAX
2. OPERATION TEMP: -20°C TO +70°C.
3. PRODUCT COMES WITH DUST CAPS. (NOT SHOWN)
4. MATERIALS:
- D SLEEVE - CERAMIC (ZIRCONIA)
HOUSING - DELRIN, BLACK
ADAPTER - THERMOPLASTIC
- E SCREWS - STEEL, ZINC PLATED
ADAPTER MOUNTING CLIPS - STAINLESS STEEL
5. FOR MOUNTING SCREWS TO BE SHIPPED WITH ASSEMBLY AND INDIVIDUAL PACKAGING, ADD SUFFIX -PKG TO PART NUMBER.
6. WHEN MOUNTING ASSEMBLY, USE A SCREW TORQUE OF 10 INCH-POUNDS MAXIMUM.
7. THIS PRODUCT IS RoHS COMPLIANT.

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.													
						SIZE	WIDTH		MULT		LBS/M		TEMPER						
E	28846	07/02/26	PC	TJK		FINISH							MATERIAL						
D	28829	05/15/26	PC	TJK		SPEC No.							SPEC No.						
C	28516	06/27/22	PC	TJK		FIRST USED ON				SCALE 1.5:1			Switchcraft®						
B	27239	1/3/14	TO	TJK		DATE DRAWN	BY	CHKD		APVD									
A	26348	2/27/09	RS	TJK		11/07/07	JGK	RS		TJK									
REV	ECO NUMBER	DATE	BY	APVD				5/21/09		7/16/09		SHEET 1 OF 1							
REVISIONS					DO NOT SCALE DRAWING					NAME E SERIES LC TO LC FIBER OPTIC ADAPTER, RoHS				PART No. EHL C2 _SERIES				REV E	