


SEARCH KEYWORD, PART NUMBER 



Part Number: 15509274

Product Name: [OCS 1.5 Unsealed](#)

2 Way F OCS 1.5 Unsealed

 [Share](#)  [Print](#) [Contact Us About This Item](#)


GET SAMPLES 

ATTRIBUTES DOCUMENTS ECAD COMPATIBLE PARTS


Attributes

Product Family OCS	Height (mm) 21.18
Product Series 1.5 Unsealed	Color BLACK
Max. operating temperature +105°C	Primary Locking Mechanism LOCKING LANCE
Min. operating temperature -40°C	Weight (g) 3.03298
No. of Ways 2	Terminal 1 Size 1.5
Cable Exit Orientation 180°	Sealing Unsealed
Gender Female	Primary Material PBT GF 20
Length (mm) 29.1	Vibration Rating V1
Width (mm) 13.82	


Other Products



35829171
2 Way Male 0.5 Unsealed Green



35829170
2 Way Male 0.5 Unsealed Violet





35829169
2 Way Male 0.5 Unsealed Blue

RESOURCE-CENTER-ITEM

COV CONN CLIP CDT BLACK



Next Steps



Keep pace with where mobility is going.

See what's next and get the latest updates.

SIGN UP TO GET UPDATES 

Don't worry. We won't flood your inbox or share your email.

INSIGHTS

EXPLORE ALL ARTICLES
CASE STUDIES
MOBILITY INSIDER
RESEARCH PUBLICATIONS
WHITE PAPERS

SOLUTIONS

Advanced Safety
Connected Services
Connection Systems
Connectivity and Security
Electrical Distribution Systems
Middleware & DevOps
Smart Vehicle Architecture
User Experience
Vehicle Electrification Systems
HellermannTyton
Intercable Automotive Solutions
Motional
Winchester Interconnect
WInd River

CATALOG

ABOUT

Our Mission
Our Businesses
Our Locations
Our Foundation
Sustainability
Suppliers

PRIVACY

Terms of Use
Cookie Policy

LEGAL & COMPLIANCE

CAREERS

INVESTORS
NEWSROOM
CONTACT