





SWITCH FUNCTION

Model No.	POS. 1	POS. 2
DPW 1 BG	ON	MOM
Term. Conn.	1 3	short
Schematic		open

PANEL CUT-OUT



RUBBER WASHER



X=CAP COLOR	
W	white
K	black
R	red
O	orange
Y	yellow
G	green
B	blue

Specifications:

Contact rating:	400mA, 32V AC max.; 100mA, 50V DC max.; 125mA, 125V AC max.
Contact resistance:	50mOhm max. at 2-4V DC, 100mA
Insulation resistance:	1GOhm min. at 500V DC
Dielectric strength:	1000V AC (50/60Hz) for 1 minute
Operating temperature:	-30°C to +85°C
Mechanical life:	1 000 000 cycles
Electrical life:	500 000 cycles
Operating force:	2-5N
Soldering conditions:	350°C max. for 5sec.
Travel:	1.5 +/-0.25mm
Water proofing:	IP 67
Torque:	1.5Nm max. applied to nut
Panel thickness:	min. 0.8 - max. 1.8mm
Material:	Case: diallyl phthalate (DAP) (UL94V-0) Cap / bushing: polyamide 6/6 Terminal / contact: gold over silver plated



Tolerances: 0.00: ±0.25mm 0.0: ±0.40mm			Date	Name	DPW 1 BG S-x	
			11/11	dr		
					knitter-switch	
					30 24 85	
Modifications	Date	Name				Page 1/1