

**Mallory Sonalert Products, Inc.**


Part #:

**JR16-G-4****Sales Outline Drawing**

Revision:

**A****Specifications:**

|                        |                                                                |
|------------------------|----------------------------------------------------------------|
| Voltage Rating         | 9 to 16 VDC                                                    |
| LED Color              | GREEN                                                          |
| LED Current Draw       | 25mA max                                                       |
| Total Max Current Draw | 25mA MAX                                                       |
| Housing Material       | 6/6 Nylon, Color: Black                                        |
| Top Cap Material       | 6/6 Nylon, Color: Opaque White                                 |
| Storage Temperature    | -40° to +70° C                                                 |
| Operating Temperature  | -30° to +60° C                                                 |
| Mounting               | Recommended hole size is 22.5 mm.                              |
| Knurled Nut            | The max recommended torque is 10 in-lbs.                       |
| Cable                  | Gray, UL Style 21894, 300V, 105°C, 24AWG, Pb-Free Tinned Leads |
| Weight (Typical)       | 105 grams                                                      |
| NEMA 12                | Approved with use of included gasket.                          |
| Options                | Please contact factory.                                        |

**Dimensions:** Inches (mm)**cUL Recognized****ROHS Compliant**

Connections:

TOP BROWN wire to Ground and GREEN wire to Positive