


416BS6

Wall mounted inlet

2CMA193307R1000



Wall mounted inlet, earthing sleeve position 6h, rated current 16A, IP44 splashproof, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red

GENERAL

Product Name	Wall mounted inlet
Product ID	2CMA193307R1000
Function	Wall mounted inlet
EAN	739269693
Catalog Description	Surface inlet, 6h, 16A, IP44, 3P+N+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421514
E-Number Norway	1542383
E-Number Sweden	E2417175
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	EBS
Color	Red
Number of Poles	5
Clock Position	6Hour
Rated Current	16 ampere
Rated Voltage	200/346 ... 240/415 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	1.5...4 mm ²
Housing Material	Plastic (PA)
Plug Angle	Angled
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	79 millimetre
Product Net Height	100 millimetre
Product Net Length	132 millimetre
Product Net Depth	132 millimetre
Product Net Weight	0.2 kilogram

PACKAGING

Package Width	154 millimetre
Package Height	378 millimetre
Package Gross Weight	2 kilogram
Package Length	182 millimetre
Package Units	box 10 piece