

[Labels](#) / [Labels by Application](#) / [Barcode Labels](#) /

3" Core High Adhesion Glossy Polyester with Rubber Adhesive Labels

3" Core High Adhesion Glossy Polyester with Rubber Adhesive Labels





Product Highlights:

Color:

White

Material Number:

B-483A [\(View Technical Data Sheet\)](#)

Finish:

Gloss

For Use with Printer:

BBP®81 Label Printer, BRADY IP® Series
Label Printer, BradyPrinter i5100,
BradyPrinter i7100, BRADYPRINTER PR
Plus Series Label Printer, THT 3" Core
Printer

Material:

Polyester

Label Properties:

Aggressive Adhesive Labels

Choose your options: [Reset Options](#)

1 Quantity per Roll

10000

2 Label/Tape Size

0.5 IN H X 1.5 IN W

Part Number:

THT-37-483-10




[View All Options](#)

ADD TO CART

+

-



Add To Favorites

People Also
Viewed



BMP21-
PLUS
Camo
[Arrow.com](#)



3" Core
Glossy
White
Polyester
Barcode
and Solar
Panel
Labels



3" Core
Continuous
High
Adhesion
Glossy
Polyester
with
Rubber
Adhesive
Labels



Thermal
Transfer 1"
Core
Polyester
Labels



Need a different size? Customize it!



Calculate how many labels you can print with one ribbon



Request product certification



Overview

Ultra Aggressive Polyester (B-483) is perfect for labeling products and general ID and can be applied to powder coated, smooth, textured or irregular surfaces.

- Glossy white polyester with permanent rubber based adhesive is thermal transfer printable
- Material is designed for high adhesion to textured metals and low surface energy plastics
- UL approved;CSA accepted
- Service temperature of -40 to 248° F (-40 to 120° C)

Specifications

Key Characteristics		157
	Product Number	31335
	UPC	662820313359
	UOM	Roll of 10000 Labels
	Quantity per Roll	10000
	Unit Price	/Label
	Trade Name	ToughBond
	Brand Name	Brady®
		Mexico
		8443.99.2550
		EAR99

Dimensions	Dimensions	0.5 in H x 1.5 in W
	Height	0.5 in
	Width	1.5 in
	Label/Tape Size	0.5 in H x 1.5 in W
	Thickness	0.004 in
	Vertical Repeat	0.6 in

Material Characteristics		B-483A (View Technical Data Sheet)
		Polyester
	Label Properties	Aggressive Adhesive Labels
	Adhesive Type	Permanent Rubber Based
	Finish	Gloss
	Color	White
	Resistance Properties	Abrasion-Resistant, Chemical-Resistant, Corrosion-Resistant, Humidity-Resistant, UV-Resistant, Weather-Resistant
	Minimum Service Temperature °F	-40 °F
	Maximum Service Temperature °F	248 °F
	Compatible Surface Types	Low Surface Energy

Product Features		Asset Tracking, Barcode Labeling, Component and Equipment Labeling, General Identification, Inventory and Inspection Labeling
------------------	--	---

	Shape	Rectangle
	Label/Media Format	Roll
	Ribbon Series	R6000HF
	Quantity per Row	2

Printing Specifications	Print Technology	Thermal Transfer
-------------------------	------------------	------------------

Compatibility	For Use with Printer	BBP®81 Label Printer, BRADY IP® Series Label Printer, BradyPrinter i5100, BradyPrinter i7100, BRADYPRINTER PR Plus Series Label Printer, THT 3" Core Printer
		IP-R6002, R6002

Compliance		55121612
------------	--	----------

Related Items

Corporate

[About](#)
[Careers](#)
[Investors](#)
[Do Not Sell My Personal Info](#)
[Privacy Policy](#)
[Terms and Conditions](#)
[ISO Certificates](#)

Other Brady Sites

[Distributor Portal](#)
[International Sites](#)
[Brand Protection Solutions](#)

Help

[Contact Us](#)
[Customer & Technical Support](#)
[Resource Center](#)
[Searchable Support Articles](#)
[Certificate Request](#)
[Website Feedback](#)

Contact

6555 W. Good Hope Rd
 Milwaukee, WI 53223

 Phone: 888-250-3082
 Hours: 7:00am–5:00pm CT
 Monday–Friday

Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and

We use cookies to ensure you get the best experience on our website. [Learn More.](#)

GOT IT!