




Isolierkörpermaterial
Nylon, UL94V-0

Kontaktmaterial
Phosphorbronze

Kontaktoberfläche
Ni, Sn

Kontaktwiderstand
20mΩ max

Isolationswiderstand
500MΩ min

Strombelastbarkeit
1A

Betriebstemperatur
-25°C - +85°C

Betriebsspannung
100V AC

Prüfspannung
500V AC

Verpackung
Stangenverpackung

Insulator material
Nylon, UL94V-0

Contact material
Phosphor bronze

Plating
Ni, Sn

Contact resistance
20mΩ max

Insulation resistance
100MΩ min




Current rating
1A

Operating temperature
-25°C - +85°C

Operating voltage
100V AC

Test voltage
500V AC

Packing
Tube packing



Bestellcode / Ordercode

Polzahlen
04 - 32

No. of contacts
04 - 32

Raster
100 - 1,00mm

Pitch
100 - 1.00mm

TVS - DIP, vertikal,
Kontakte einseitig

TVS - DIP, vertical,
single sided contacts

Verpackung
T - Stange

Packing
T - Tube

AFFC10 **xx** - **100** - **TVS** - **x**

Bitte „x“ durch die geeignete Option ersetzen
Please replace „x“ with appropriate option