




PD Series

[all categories](#) > [through hole technology](#) > [socket pin](#) > [pd series](#) > PD-61

[Save To Favorites](#)
[Download Catalog](#)



Socket Pin - PD-61

- Confirm applicable male pin diameter before use.
- Contact Resistance.....10m ohm or less
- Depth (mm)....4.2
- Finish....
Contact part..Au p
Body part..Sn p
- Material....
Contact part..Beryllium copper
Body part..Brass
- Mating/unmating (durability)....100 or more
- Mating/unmating Forces (g or more)....150
- Rated Current (A)....5
- Rated Voltage....125V AC, DC
- Recommended Male Pin Diameter (phi mm)....0.6 to 0.8
- Recommended Through-hole Diameter (phi mm)....0.7
- Temperature Range (Degrees Celcius)....-40 to +125

[>> request quote / information](#) | [>> download specs](#)