



Part Number : [1063591002](#)
Product Description : Quasar OptiX Field Mountable Connector (FMC), SC/APC, Singlemode, for 250/900µm Bare Fiber, Green Housing
Series Number : 106114
Status : Active
Product Category : Fiber Optic Connectors



Documents and Resources

Drawings

[1063591002_sd.pdf](#)

Specifications

[1063591001_INS-DTL-000.pdf](#)

[1063591001_INS-FLD-000.pdf](#)

[1063591001_PS-000.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Fiber Optic Connectors
Series	106114
Description	Quasar OptiX Field Mountable Connector (FMC), SC/APC, Singlemode, for 250/900µm Bare Fiber, Green Housing
Keyword	FMC
Mode	Singlemode
Product Name	Quasar OptiX Field Mountable Connector
UPC	198282245667

Physical

Angled Physical Contact (APC)	Yes
Boot Color	White
Boot Type	Straight
Cable Size	250µm, 900µm
Color - Resin	Green
Ferrule Hole Size	N/A
Ferrule Material	Ceramic
Gender	Plug
Material - Housing	PBT
Mounting Style	Pre-Polished
Net Weight	3.273/g
Ports	1
Wire/Cable Type	Simplex