



Active

 Add to Part List

Not EU RoHS or ELV Compliant

- 7000 Electropneumatic Timing Series
- Time Delay Relay
- Input Voltage = 110 VAC, 120 VAC
- Contact Arrangement = 4 Form C, 4PDT, 4 C/O
- Contact Rating = 10A @ 240 VAC

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

- None Available

- None Available

- None Available

- None Available

- [7000 Series 4-Pole Timing Relay \(PDF, English\)](#)

- None Available

- Product Line Information

- Tooling

List all Documents

- Product Type = Time Delay Relay
- Termination Type = Screw Terminal

- Input Voltage (VAC) = 110, 120
- Contact Rating = 10A @ 240 VAC

- **Series** = 7000 Electropneumatic Timing

- Mounting Options = Panel Mount
- Mode of Operation = On-Delay
- Delay Time = 3 minutes to 30 minutes
- Type of Control = Knob
- Repeatability, Max. = $\pm 10\%$
- Approved Standards = CE Approved, CSA Certified, FM Approved, UL Listed
- Approx. Dimensions (L x W x H) (mm [in]) = 114.80 x 65.30 x 71.90 [4.523 x 2.572 x 2.832]

- Contact Arrangement = 4 Form C, 4PDT, 4 C/O
- Multiple Timing Ranges = Without

- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Not relevant for lead free process

- Temperature Range ($^{\circ}\text{C}$) = $-30 - +75$

- Brand = Agastat