


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/13/2020	MBLACKWOOD
B	UPDATE CABLE TEMP RATING	3/7/22	DGUST



NEMA L6-20P
E257089

(UL) C(UL) SJT 14AWGx3C 60°C 300V
FT2 E313867




IEC C13 15A 250V
E257089

PART NUMBER	L FEET	L METERS
PPA00017-3FT	3	0.91
PPA00017-6FT	6	1.83
PPA00017-8FT	8	2.44
PPA00017-10FT	10	3.05

NOTES:

1. APPROVALS: UL, cUL.
2. RATING: 15A/250V.
3. COLOR CODING: BLACK, WHITE, GREEN.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH SPEC. PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		 an INFINIT [®] brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY DZINN		10/13/2020		CATEGORY		POWER PRODUCTS		
		CHECKED BY DFRISIELLO		10/13/2020						
		APPROVED BY MBLACKWOOD		10/13/2020						
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [.5] ± 1/32 .XXX = ± .005 [.13] ANGLES ± 1°		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION Nema L6-20P to C13 Power Cord, 15A, 250V						
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		SIZE A		CAGE CODE 43321		ITEM NO. PPA00017		REV. B
				SCALE: NONE		CAD FILE: PPA00017.SLDDRW				SHEET 1 OF 1