

SATO PARTS CO.,LTD. > Product Category > LED bracket / Neon bracket > Neon bracket

Product mass

Precautions for use

General notes

BN-3802

made in JAPAN



2012-06-01

Notice of partial product changes. PDF



See other change notifications

Order model number

Order model number

BN-3802-[Voltage]-[Lens color]

Order example

BN-3802-1-R (An example of ordering with a red lens with a voltage of AC100-125V.)

BN-3802-2-R (An example of ordering with a red lens with a voltage of AC200-250V.)

Basic information

Dimension

Soldering heat resistance conditions

Download

Lens color



R



G



OR

Add to My List



Sample request (Only available in Japan)



*The lighting color of the lens color C is orange.

Basic information

Rating	AC100V~125V、AC200V~250V
Insulation resistance	DC500V、100MΩ Min
Withstand voltage	AC1500V (1minute)
Life	20000 hours Min (Serial lighting)
Body material	Brass
How to mount	With nut
Main insulator	PBT (UL94V-0)
Terminal type	Soldering
Lens color	R (Red)、G (Green)、OR (Orange)、C (Clear)
Panel thickness	7.0mm (MAX)
Nut torque	0.7N・m
Caution	1.When soldering, please solder with the lug facing down or horizontal.

List of partial product change notifications

2012-06-01	Notice of partial product changes. PDF
2010-03-25	Notice of partial product changes. PDF

Related products

BN-35



BN-35

Add to My List

BN-5665



BN-5665

Add to My List

BN-5668



BN-5668

Add to My List

BN-5701



BN-5701

Add to My List

Home

Product search

Product Category

About SATO PARTS

News classification

Contact us

Video channel

Download brochure

Environmental initiatives

Privacy policy

Cookie policy

Download terms

Terms of Use