





1.Wiring Diagram.



2.Cable test condition :

Open / Short : 100%

Insulation resistance : 5M ohms

Contact resistance : 2 ohm

Hipot : DC 300V / 1 sec

3.Each pcs with PE polybag.

7	COPPER	COPPER FOIL 20X40MM	1			B	2020001	ADD COPPER FOIL	2020/05/07
6	COPPER	COPPER FOIL 15X40MM	1			A		INITIAL RELEASE	2014/08/28
5	CONN	USB3.0 MICRO B MALE G/F BLACK	1	P2		REVISION#		DESCRIPTION	DATE
4	PVC	45P PVC BLACK OVERMOLD	25g			P/N:		103-1092-BL-00300	REV B
3	PE	LLDPE 500026 6201	16g			TITLE		CABLE USB3.0 A/M TO MICRO B MALE	
2	CONN	USB3.0 A/M G/F BLUE	1	P1		CUSTOMER P/N:			
1	CABLE	《28AWG (7/0.12TC) *1P+D(7/0.10TC)+AL+M》*2+28AWG (7/0.12TC) *1P+24AWG(7/0.2TC)*2C+A+D+B (96/0.12AM) ODS.5 BLACK	1	3000mm		DRAWN	WENC	DATE	08/24/14
NO.	PART NO.	DESCRIPTION	QTY	UNIT/REF	CHECKED	EDWIN	08/24/14	CUSTOMER:	
BILL OF MATERIAL									
SHEET 1 OF 1									