


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	REVISED PER ECO-17-015605	25OCT2017	RS	DR



1 STAMP AMP 12-10* APPROX AS SHOWN.


2 MAX FEATURE LENGTH DOES NOT INCLUDE MANUFACTURING TABS.

500	LOOSE PIECE	325167
QTY	PACKAGE TYPE	PART NO.

MAX RECOMMENDED
OPERATING TEMPERATURE:
170°C [338°F]

VOLTAGE RATING:
N/A

CIRCULAR MIL AREA:
2.62–6.64mm² [5,180–13,100]
SOLID OR STRANDED

DIMENSIONS:		DWN	RAVI S	25OCT2017	MATERIAL	COPPER ANNEALED PER ASTM B152	FINISH	TIN PLATE, 0.00254[.000100] MIN EXT. THK. PER ASTM B545		
mm [INCHES]		CHK	ROHDE DANIEL F	25OCT2017	 TE Connectivity					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	ROHDE DANIEL F	25OCT2017						
		PRODUCT SPEC		NAME					BUTT SPLICE, SOLISTRAND, NO WIRE STOP, 12-10 AWG	
0 PLC ± -		APPLICATION SPEC			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
1 PLC ± -		2 PLC ± -			A4	00779	C= 325167	—		
2 PLC ± -		3 PLC ± 0.127[.005]								
3 PLC ± -		4 PLC ± -								
4 PLC ± -		ANGLES ± -								
		WEIGHT		—						
		CUSTOMER DRAWING					SCALE	4:1	SHEET	1 of 1