

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

SWITCH - ENCLOSED

CATALOG LISTING
BZE6-2RQ841-BP

M BZE6-2RQ841-BP

DRAWING
NUMBER

ISSUE
X15

REPLACES

RELEASE NO. PR-19685

29AUG07

PSR

CHECK

10 NOV 05

RJ

CHECK

11 DEC 91

TSM

CHECK

10 DEC 91

MAM

RASTER
DRAWN

REVISIONS

A CO 72618

TSM

18 SEP 92

B CO 73655

TSM

22 APR 93

C 0016894



KRB

10 NOV 05

D 0033014


BS

29AUG07



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

THIRD ANGLE PROJECTION



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±

WEIGHT .56 LB

CHARACTERISTICS

OPERATING FORCE — — — — — 9-13 OZ
RELEASE FORCE — — — — — 4 OZ MIN
DIFFERENTIAL TRAVEL — — — — .002 MAX
OVERTRAVEL — — — — — .140 MIN
SWITCH - BASIC REPLACEMENT--BZ-2RQ784

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L74 15A 125, 250 OR 480 VAC
2A 600 VAC
1/8HP 125 VAC, 1/4HP 250 VAC
1/2A 125 VDC, 1/4A 250 VDC

CE 1.5A, 240 Vac



NOTE

- 1 - 3X 6-32 UNC X (.219) BINDING HEAD TERMINAL SCREW
AND CUPWASHER
2 - SEAL RATING: NEMA 1
IP40

ANSI Y14.5M-1982 APPLIES