



Front Panel, front anodized and conductive, shieldable (textile), screw assembly



Other Views



Catalog Number: 20848-068

Back To Product

- Difference in finish between 2 ... 12 HP and 14 ... 84 HP
- U profile front panel for increased rigidity
- Front panel, U profile, Al, front anodized, rear conductive
- 2 alignment pins pressed-in (not 2 and 84 HP front panels)

Note:

- Please order fixing material (sleeves, collar screws) separately, see Downloads-Mounting Hardware
- 14 ... 84 HP: multi-part U-profile (front panel with crimped profiles)
- Differences in finish between 2 ... 12 HP and 14 ... 84 HP
- 2 ... 12 HP: one-part U-profile
- Please order textile EMC gasket separately
- Standard pack quantity: 2 to 28 HP: 5 pieces, 42 to 84 HP: 1 piece, supplied in standard pack quantities (SPQ) only

Specification:

- IEEE 1101.1/10
- IEC 60297-3-101

Material and Surface Finish:

Al, Front Anodized, Rear Etched

Assembly:

Screw on - Front Side

EMC Shielding:

Shieldable (Textile Gasket)

Type:

Individual Components

Individual Component Type:

Front Panels



Select product specifications before modifying or adding to project list or requesting a quote.

Height-U-defining

3 ▾

Width-HP-defining

63 ▾

[Clear Selection](#)

Quantity

1

Modify Product ▶

Add Item to Project List +

Documents



Links











Technical Data



Height mm	128.4
Qty	1 piece
b1 mm	304.8
b2 mm	157.5
B mm	319.7
For case height [U]	128.4
Thickness mm	2.5
Height U	3
Width HP	63

Delivery Comprises:

Item	Quantity	Description
1	1	Front panel, U profile, Al, front anodised, rear conductive, 2 alignment pins pressed-in, stainless steel

Accessories

	Collar screw, cross recess/slotted (M2.5x12.3), steel black, PU 100 pcs	21101-102	Add Item to Project List +
	Collar screw, cross recess/slotted (M2.5x12.3), steel nickel plated, PU 100 pcs	21101-101	Add Item to Project List +
	Collar screw, Torx (M2.5x12.3), steel black, PU 100 pcs	21101-783	Add Item to Project List +
	Sleeve, plastic, black, PU 100 pcs	21100-591	Add Item to Project List +
	Sleeve, plastic, grey, PU 100 pcs	21100-464	Add Item to Project List +
	Quarter-turn fastener with knurled and slotted head, grey, PU 100 pcs	21101-849	Add Item to Project List +
	Quarter-turn fastener with slotted head, grey, PU 100 pcs	21101-847	Add Item to Project List +
	Collar screw, knurled head short (M2.5x12.3), brass nickel plated, PU 100 pcs	21101-749	Add Item to Project List +
	Collar screw, Torx (M2.5x12.3), steel nickel plated, PU 100 pcs	21101-782	Add Item to Project List +
	Sleeve, stainless steel, PU 100 pcs	21100-662	Add Item to Project List +
	Quarter-turn fastener with knurled and slotted head, black, PU 100 pcs	21101-850	Add Item to Project List +

	Sleeve, brass, black, PU 100 pcs	21100-886	Add Item to Project List +
	Quarter-turn fastener with slotted head, black, PU 100 pcs	21101-848	Add Item to Project List +
	Sleeve, brass nickel-plated, PU 100 pcs	21100-660	Add Item to Project List +
	Collar screw, knurled head long for LD (M2.5x12.3), brass nickel plated, PU 100 pcs	21101-909	Add Item to Project List +
	EMC shielding textile gasket, -40...+70°C, 3 U, PU 10 pcs	21101-853	Add Item to Project List +
	EMC shielding textile gasket, -40...+70°C, 3 U, PU 100 pcs	21101-854	Add Item to Project List +

EXPLORE	CONTACT	DOWNLOAD
About Us	Customer Service	Download Center
Services & Capabilities	Find a Sales Office or Distributor	Reference Projects
News & Events	Global Locations	Videos
Newsletter Subscriptions	Product Compliance & Certifications	Product Configurators
Strategic Partnerships	Partner Login	Warranties and Terms of Sale & Procurement
Investor Relations		