


MAC3

product search

products | support | company | contact us


THROUGH HOLE TECHNOLOGY

SURFACE MOUNT TECHNOLOGY



MX Series

uper small) > mate/unmate with ME, MF, PM series,



Mate/unmate with ME, MF, PM series, Pitch=1.27, 1.778, :

- 1.27, 1.778, 2.0, 2.54mm pitch are available.
- Applicable Socket Pin....ME, MF series
- Dielectric Strength....
1000V AC, DC 1min
700V AC, DC 1min (MX-1 series)
- Finish....Pin part..Au plating over Ni
- Insulation Resistance....500M ohm or more
- Material....
Resin part..PCT black (UL94V-0)
Pin part..Phosphorus bronze
- Rated Current....2A
- Recommended Through-hole Diameter (phi mm)....0.6
- Temperature Range (degrees Celsius)....-40 to +125


☐ Save To Favorites

☐ Download Catalog


MX-x-0 to MX-x-4

>> request quote / information | >> download specs

	L (mm)	A (mm)	P (mm)	Max Pins	H (mm)	Applicable Socket Pin
MX-1-0	3.0		1.27	40		-----
MX-1-1	3.7		1.27	40	5.7	ME-1-1
MX-1-2	4.4		1.27	40	5.9	ME-1-1
MX-1-3	4.9		1.27	40	6.4	ME-1-1
MX-1-4	5.4		1.27	40	6.9	ME-1-1
MX-2-0	3.0		1.778	30		-----
MX-2-1	3.7		1.778	30	3.5	ME-2-1
MX-2-2	4.4		1.778	30	4.0	ME-2-1
MX-2-3	4.9		1.778	30	4.5	ME-2-1
MX-2-4	5.4		1.778	30	5.0	ME-2-1
MX-3-0	3.0		2.54	20		-----
MX-3-1	3.7		2.54	20	3.5	ME-3-1 MF-3-1
MX-3-2	4.4		2.54	20	4.0	ME-3-1 MF-3-1
MX-3-3	4.9		2.54	20	4.5	ME-3-1 MF-3-1
MX-3-4	5.4		2.54	20	5.0	ME-3-1 MF-3-1
MX-1-5	3.8	3.0	1.27	40	7.5	ME-1-1
MX-1-6	3.8	3.5	1.27	40	8.0	ME-1-1
MX-1-7	3.8	4.0	1.27	40	8.5	ME-1-1



MX-x-5 to MX-x-10



MX-3-6	3.8	3.5	2.54	20	6.0	MF-3-1
MX-3-7	3.8	4.0	2.54	20	6.5	ME-3-1 MF-3-1
MX-3-8	3.8	1.778	2.54	20	7.0	ME-3-1 MF-3-1
MX-3-9	3.8	5.0	2.54	20	7.5	ME-3-1 MF-3-1

*H is the space between PCBs with ME, MF series.

***HOW TO ORDER**

MX-1-1-10P

Put # of pins if necessary.