




Part Number : [358421301](#)
Product Description : PT Bulb Socket, Double
Housing Assembly, Type A, Sealed, Black
Series Number : 35842
Status : Obsolete
Product Category : Sockets

Documents and Resources

Drawings

[358421301_sd.pdf](#)

Specifications

[PK-35842-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Duty-To-Declare
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

Part Details

General

Status	Obsolete
Category	Sockets
Series	35842
Description	PT Bulb Socket, Double Housing Assembly, Type A, Sealed, Black
Comments	A-Type
Component Type	Socket
Product Name	Bulb Socket
UPC	756054202869

Electrical

Current - Maximum per Contact	5.0A, 7.0A
Voltage - Maximum	12V

Physical

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
Durability (mating cycles max)	30
Entry Angle	Vertical
Keying to Mating Part	No
Material - Metal	Phosphor Bronze
Material - Resin	Nylon
Net Weight	11.200/g
Packaging Type	Bag
PCB Locator	No
PCB Retention	N/A
Pitch - Mating Interface	N/A
Pitch - Termination Interface	N/A
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	Lamp

Use with Part(s)

Description	Part Number
Positive Terminal for PT Bulb Socket, AVSS 0.50~0.85mm ²	<u>354648000</u>
Earth Terminal for PT Bulb Socket, AVSS 0.50~0.85mm ²	<u>354658000</u>
Positive Silicone Rubber Wire Seal for Sealed PT Bulb Socket	<u>359030096</u>
Earth Silicone Rubber Wire Seal for Sealed PT Bulb Socket	<u>359030106</u>

This document was generated on Sep 22, 2026