

416RU6

Panel mounted socket

2CMA193187R1000



Panel mounted socket, earthing sleeve position 6h, rated current 16A, IP44 splashproof, unified flange, straight, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red

GENERAL

Product Name	Panel mounted socket
Product ID	2CMA193187R1000
Function	Panel mounted socket
EAN	7392696931878
Catalog Description	Socket-outlet, panel mounting, 6h, 16A, IP44, unified flange, straight, 3P+N+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421237
E-Number Norway	2416633
E-Number Sweden	E2416633
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	75 millimetre
Product Net Height	89 millimetre
Product Net Length	91 millimetre
Product Net Depth	91 millimetre
Product Net Weight	0.22 kilogram

TECHNICAL

Product Main Type	ERU
Color	Red
Number of Poles	5
Clock Position	6Hour
Rated Current	16 ampere
Rated Voltage	200/346 ... 240/415 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	1.5...4 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

PACKAGING

Package Width	138 millimetre
Package Height	345 millimetre
Package Gross Weight	2.2 kilogram
Package Length	158 millimetre
Package Units	box 10 piece