


HH-1 Series

[products](#) > [connector for surface mount board](#)



[request quote / information](#) | [download specs](#)


Connector for Surface Mount Board

- Outputting each signal line separately can make layout design flexible.
- Can mount vertically and horizontally
- Adaptive Male Pin...HJ-1
Heat Shrinkable tube for HJ-1...HJ-T
Cramp...HH-1-R
- Contact Resistance....10m ohm and below
- Durability....100 Times and over
- Finish....
HH-1-G..Body..Plated Au over Ni base
HH-1-G..Contact..Plated Au over Ni base
HH-1-S..Body..Plated Sn over Ni base
HH-1-S..Contact..Plated Au over Ni base
- Insertion Power....70g and over
- Material....
Body..Brass
Contact..Beryllium Copper
- Rated Current....1A
- Recommended Male Pin Diameter (phi mm)....0.45 to 0.6
- Removal Power....70g and over
- Temperature Range (Degrees Celcius)....-40 to +125

[Save To Favorites](#)
[Download Catalog](#)

N/O	Package
HH-1-G	100pcs/pack
HH-1-G-P	100pcs/stick
HH-1-G-T	2000pcs/reel
HH-1-S	100pcs/pack
HH-1-S-P	100pcs/stick
HH-1-S-T	2000pcs/reel

Recommended Diameter



*Notice

Before mounting, please confirm from which side socket appears.

