

Vertical Cable Management D-Rings

specifications

A vertical cable management solution of flexible D-rings shall be used on standard communication racks. The vertical D-rings used for open access shall be manufactured from a polycarbonate material and shall be black in color. The vertical cable management D-rings shall be a one-piece design. The front arm of the product shall be able to rotate ninety degrees to allow entire cable bundles to be inserted. The vertical cable management solution of flexible D-rings shall be installed with two screws less than 0.25" diameter.



technical information

Dimensions:

Part Number	Height In. (mm)	Width In. (mm)	Depth In. (mm)
CMVDR1	2.38 (60.5)	2.05 (52.1)	5.72 (145.2)
CMVDR1S	2.38 (60.5)	2.05 (52.1)	3.26 (82.8)
CMVDR2	2.38 (60.5)	3.30 (83.8)	5.72 (145.2)
CMVDR2S	2.38 (60.5)	3.30 (83.8)	3.26 (82.8)
CMVDRC	1.75 (44.5)	8.75 (222.3)	5.66 (143.8)

Capacity:

Part Number	Channel Area (in²)	Cat. 6A (28AWG – 0.185")	Cat. 6A (24AWG – 0.275")	Cat. 6 (28AWG – 0.150")	Cat. 6 (24AWG – 0.235")
CMVDR1	7.1	105	47	160	65
CMVDR1S	3.5	52	23	80	32
CMVDR2	14.5	215	97	328	133
CMVDR2S	7.1	105	47	160	65
CMVDRC	30.1	447	202	680	277

Packaging:

Packaged one per bag

Standards:

Meets all EIA requirements as defined in EIA-310D; manufactured from a material that meets UL94-V0 specifications

key features and benefits

EIA mounting holes	Capable of being applied to any standard EIA rack system
Flexible arm	Provides open access that allows installation of complete cable bundles
Rounded edges	Prevents sharp edges in contact with cable insulation
1/4" screw holes	Utilize a wide variety of screws to secure product to wall or rack

applications

Panduit Vertical Cable Management D-rings are designed to contain cables in a vertical pathway. The cable management D-rings are a labor-saving solution that provides the installer the ability to insert complete cable bundles.

Use these vertical D-rings in conjunction with horizontal D-rings for a complete open access solution on rack systems. Products may also be mounted onto a wall or other flat surfaces with a variety of screws.

Vertical D-rings

1":	CMVDR1
1" short:	CMVDR1S
2":	CMVDR2
2" short:	CMVDR2S
Center:	CMVDRC

Racks

19" rack:	R2P
23" rack:	R2PW

Horizontal D-ring Systems

2RU front and rear:	CMPH2
2RU front:	CMPHF2
1RU front and rear:	CMPH1
1RU front:	CMPHF1


Accessories

12-24 mounting screws:	S1224-C
Flat post standoff:	PPF2S-S25-V
Flat post standoff flame retardant:	PPF2S-S25-V69
Flat post standoff Tak-Ty® Cable Ties compatible:	PPF2SV-S25-V
Flat post standoff Tak-Ty® Cable Ties compatible flame retardant:	PPF2SV-S25-V69
Bend radius clip:	CMSRC2
1RU strain relief clip:	WMSRC1
2RU strain relief clip:	WMSRC2
Bundle retainer:	BR2-1.3
Adhesive bundle retainer:	BR2-1.3-A

Installer Tip:
CMVDRC requires 8.25" center to center hole spacing for adjacent racks.

Vertical Cable Management D-Rings

mounting configurations



- 1 CMVDR1
- 2 CMVDR1S
- 3 CMVDRC mounted to front of rack
- 4 CMVDRC mounted to front of rack and CMVDRC mounted to back of rack
- 5 Two CMVDRC parts mounted to front of rack; one opens toward the back
- 6 CMVDR2
- 7 CMVDR2S

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT[®]

©2016 Panduit Corp.
ALL RIGHTS RESERVED.
WASP40--WW-ENG
Replaces SA-WASP1035B
7/2016