


Part Number : [1041280610](#)

Product Description : IllumiMate 1.00mm Pitch
Wire-to-Board Crimp Housing, Single Row, Side Lock, 6
Circuits, Natural

Series Number : 104128

Status : Obsolete

Product Category : Connector Housings



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Connector Housings
Series	104128
Description	IllumiMate 1.00mm Pitch Wire-to-Board Crimp Housing, Single Row, Side Lock, 6 Circuits, Natural
Application	Wire-to-Board
Component Type	Receptacle
Product Name	IllumiMate
UPC	889056135467

Physical

Circuits (maximum)	6
Color - Resin	Natural
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	0.071/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	N/A
Pitch - Mating Interface	1.00mm
Temperature Range - Operating	-25° to +130°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
IllumiMate 1.00mm Pitch Wire-to-Board Header, Surface Mount, Single Row, Vertical, Side Lock, 6 Circuits	<u>1041270620</u>

Use with Part(s)

Description	Part Number
IllumiMate 1.00mm Wire-to-Board Receptacle Terminal, Pre-plated, Tin (Sn)	<u>1045398002</u>

This document was generated on Sep 17, 2026

Obsolete