

PRODUCT TOP | CATEGORY | SPECIFICATIONS | INDUSTRIES | SERIES NAME

Enter Keyword, Product name or HRS code.

SEARCH

Product Top > LF series > LF07WBP-3S(31)



RoHS2

- ▶ Product Numbers by Series
- ▶ Part Number Configuration

LF07WBP-3S(31)

Product	LF07WBP-3S(31)
Series	LF
Connector Type	Plug
Safety Standards	UL
Water Resistance	IP 68
Salt Spray Test Duration (Corrosion Resistance)	48 h

Detailed Specifications

Last Updated On Apr. 20, 2018

▼ Product information	
Part No.	LF07WBP-3S(31)
CL No.	CL0136-0003-7-31
▼ Basic information	
Connector Type	Plug
Safety Standards	UL
Water Resistance	IP 68
Salt Spray Test Duration (Corrosion Resistance)	48 h
Number of Positions	3
Contact Plating	Gold
Mating/Unmating Cycles	1000
Rated Current	5 A
Rated Voltage (AC)	AC 125 V
Rated Voltage (DC)	DC 175 V
Connector Orientation	Straight

Download

 DRAWING(2D)

▶ more

ADD TO MY LIST

▼

REQUEST FOR SAMPLE

CONTACT US

Browsing History



Series: LF

Product: LF07WBP-3S(31)

Locking Style	Bayonet
Recommended Wire Size (AWG)	AWG 20
Shell Material	Metal
Operating Temperature	-25 to 85 °C
▸ Mechanical Specifications	
▸ Electrical/Optical Specifications	
▸ Dimensional Information	
▸ Packaging Specifications	

Download

Catalog	Product Series Catalog	 DOWNLOAD
Data Sheet	Drawing (2D)	 DOWNLOAD
	3D Model (IGES)	Not Available  CONTACT
	3D Model (STEP)	Not Available  CONTACT
	Specification Sheet	 DOWNLOAD

*I [need help](#) with a product or information

- [Product Top](#)
[About Us](#)
[Specifications](#)
[Industry](#)
[Series Name](#)
[Partners](#)
- [Global Site](#)
[Terms of use](#)



© 1999-2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.

SUPPORT

[FAQ](#)

[CONTACT US](#)

