



search



live chat  offline

[HOME](#)

[CURRENT](#)

[COMPANIES](#)

[DOWNLOAD](#)

[PRODUCTS](#)

[DISTRIBUTORS / DISTRIBUTORS](#)

[DISTRIBUTION](#)

[CONTACT](#)

[BACK](#)



SF3F-01GI-P2.0

Description: **AWG 24-20 0.8AU stripform**

Crimp contact J3xx Receptacle

specification

Grid (mm)	3.81 / 5.08
Connector Type	WtW / WtB
Current (A)	9.5
Voltage (V)	600
Cross-section (AWG)	24-20
Lying version	0
Straight version	0
Water poof	0
Single row	0
Double row	0
ZIF	0
Non-ZIF	0

[UP](#)

Products

[FOR PC BOARD](#)
[WIRE TO WIRE](#)
[WATERPROOF CONNECTORS](#)
[LOOSE PIECE TERMINALS](#)
[CHAIN TERMINALS](#)
[CARD AND INTERFACE CONNECTORS](#)
[HIGH VOLTAGE SHIELDED SEALED CONNECTOR](#)
[AUTOMOTIVE](#)

information

[DOWNLOAD](#)
[IMPRINT](#)
[DATA PROTECTION](#)

Newsletters

V ornam e

Nachnam e

E-Mail A dresse

[Sign in](#)

