

[Products](#)[Customize Your Parts](#)[Industries Solutions](#)[Search](#)[News & Events](#)[First Time?](#)[Home](#) / [Products](#) / [X-Lok](#) / [Mini Size](#)

Product Line

[Single Pair Ethernet](#) >[ZConnect](#) >[Ceres](#) >[X-Lok](#) >

- Accessory
- Middle Size
- Mini Size
- Large Size
- Standard Size

[M Series](#) >[FLOS & FLOS+](#) >[Power](#) >[RBL](#) >[HS-Lok](#) >[NMEA 2000](#) >[Heavy Duty Shielded](#) >[RJ](#) >[USB](#) >[D-Sub](#) >[HDMI](#) >[DVI](#) >[Fiber Optic](#) >[RF](#) >[Cable Joiner](#) >[Cable Gland](#) >[Pressure Relief Vent](#) >[LED Light Guide](#) >[D-Sub](#) >

AZ-17PMMP-QC8001

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: N/A

Certificate: N/A

You must login first to view the price


Quantity

- 1 +

Check Stock

Add to Cart

Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

X-Lok, Mini Size, Plastic...
AB-AZ17FL-AZFL-QC001
-40°C ~ +105°C

X-Lok, Mini Size, Plastic...
AB-AZ17FL-AZFL-...
-40°C ~ +105°C

X-Lok, Mini Size, Plastic...
AB-AZ17FL-AZFL-...
-40°C ~ +105°C

X-Lok, Mini Size, Plastic...
AB-AZ17FL-AZFL-...
-40°C ~ +105°C

Specifications	Download / CAD
Nominal Current 1.5A	Connector Type Receptacle
Shielded Plastic, Non-shielded	No. of Contacts 17
Connector Gender Male	Backshell Circular
Mating Style Push Lock	IP Rating IPX8
Assembly Style PCB 180°	
More Options	

People Also Bought

