



USA/English | [Select a country](#)

[Sign In/Register](#)

[HOME](#)

[PRODUCTS](#)

[SUPPORT](#)

[ABOUT US](#)

[NEWS](#)

[CONTACT](#)

Part Number Search

[SEARCH](#)

[HOME](#) > [Industrial Components](#) > [Switches & Pilot Devices](#) > [CW Series](#) > [CW1P-1EQ4G](#)

Product Families

- ▶ [Automation](#)
- ▶ [Industrial Components](#)
- ▶ [LED Lighting & Signaling](#)
- ▶ [Machine Safety](#)
- ▶ [Sensing](#)

CW1P-1EQ4G Pilot Light 22MM 24V G

[Add to Cart](#)



Key Features

- ø22.3mm mounting hole compliant with IEC 60947-5-1
- 3.5-mm operator travel for pushbuttons ensures comfortable and reliable operation
- Black and metallic bezels available
- Illuminated pushbuttons, pushbuttons, pilot lights, selector switches and key selector switches are available
- Direct opening NC contact
- 10A contact rating; up to three contact blocks for non-illuminated and two contact blocks for illuminated models can be connected
- Up to 6 contacts per switch
- UL Type 4X rating



Specifications

Literature

Downloads

Price and Availability

Product Type	Pilot Light
Mounting Hole Size	22mm
Shape	Round
Ingress Protection Rating	IP65 degree of protection (IEC 60529) from panel front
Illumination Voltage	24VAC/DC
Lamp Type	LED
Pilot Light Color	Green