

サトパツ
SATO PARTS

2010.07.22

Recruitment
information
site map

注意事項・ヒント/
製品一部変更届

お問い合わせ

WEBSHOP

カタログ・DXFファイル
請求について

会社概要・沿革

環境に対する取り組み

新商品

販売中止品

スクリーレス端子台
Screwless Terminal
[ML/SL]

ネジ式端子台
Screw Terminal
[ML]

ヒューズホルダー
／ヒューズ管
Fuse Holder, Fuse
[F]

表示灯
Indicator
[DB/BN]

ツマミ
Knob
[K]

コンセント・コネクタ
Connector
[CN]

ターミナル
／チップジャック
Terminal, Chip Jack
[T/TJ]

アクセサリ
Accessories
[SA]

その他
Socket, Clip, Plug,
Bushing, Lug
[S/C/P/BU/L]

English Site

TJ-560



Information on RoHS
Directive

Solder heat resistance
condition

Body color



specification

Rating	30V-3A
Withstand voltage	AC 500 V (1 minute)
Insulation resistance	DC 500 V, 50 MΩ or more
Main insulating material	High Impact Styrole
Body color	B (black), R (red), BL (blue), Y (yellow), G (green), W (white)
Conforming product	TJ-4 , TJ-563

Notes

[PDF](#) Terminal・tip jack notes

[PDF](#) General remarks

Order number TJ - 560 - [Body color]

Order example TJ - 560 - R (when ordered in red)

Product partial change notice

2010/07/22 [PDF](#) Integration of metal parts (shaft and center pin)

Dimensional drawing




Screw-less terminal Adoption

[Contact Us](#)

[↑ To the top of the](#)

page



Unit: mm

DXF file / Environmentally hazardous substance report download

* Please download the [DXF file usage agreement](#) when downloading DXF file .
※ For environmentally hazardous substances report, [commitment to the environment](#) please visit.

Model number	DXF file	Environmentally hazardous substance report
TJ-560	Download [History]	
TJ-560-B		Download [History]
TJ-560-BL		Download [History]
TJ-560-G		Download [History]
TJ-560-R		Download [History]
TJ-560-W		Download [History]
TJ-560-Y		Download [History]

Updated: 2016/07/19

All contents posted on this site are prohibited without permission or diversion.

[site map](#) [About conditions of use of this site](#)

E-Mail: marketing@satoparts.co.jp Customer consultation desk 0120-70-7215
Copyright (c) 2001-2017 SATO PARTS CO., LTD. All Rights Reserved.



Screw-less terminal Adoption

[Contact Us](#)

[↑ To the top of the](#)

page